

Synthetic, absorbable, monofilament suture, presented in violet or undyed.

P-dioxanone polymer.

Offers minimal tissue reactivity.

Absorption occurs through slow hydrolytic action completed in approximately 180- 200 days.

The material retains approximately 70% of its tensile strength by the 4th week, and 50% by the 6th week.

Color code: Silver.

Frequently used in tissue coaptation requiring a longer healing period.

CHARACTERISTICS + BENEFITS

High tensile strength = Excellent tissue support.

Absorption through hydrolysis = Predictable absorption rate and minimal tissue reaction.

Excellent knot coupling = Provide excellent security.

Hermetically sealed packaging = Ensured stability and sterility of the product.

ABOUT

Recommended for any surgical procedures requiring a single-thread, synthetic, absorbable suture.

KNOTTING: When used with thick gauges (2, 1, 0, 2-0) it is preferable to tie both a surgeon knot and simple knot. This will allow the surgeon to adjust the tension accordingly. Once adjusted, an additional square knot is recommended according to the surgical circumstances and the surgeon experience.

When applied in thin gauges (3-0, 4-0, 5-0, 6-0, 7-0), initially two square knots are recommended with 2 or 3 additional bowknots, leaving the ends of the knots 4 to 5 mm long subject to the surgical circumstances and the surgeon experience.

Absorbable Sutures
Atramat®PDX
Polydioxanone



Absorbable Sutures

Atramat®PDX
Polidioxanona



Sutura sintética, absorbible, monofilamento en color violeta e incoloro.

Compuesto de polímero de P-dioxanona

Ofrece mínima reactividad tisular.

La absorción ocurre a través de una acción hidrolítica progresiva que se completa entre 180-210 días.

El material mantiene su resistencia tensil al 70% en la 4ta semana y al 50% en la 6ta semana.

Código de Color: Plata.

Frecuentemente utilizado en tejidos con periodo de cicatrización largo.

CARACTERÍSTICAS + BENEFICIOS

Alta Resistencia tensil = Excelente soporte al tejido

Absorción por hidrólisis = Tasa de absorción predecible y mínima reactividad tisular

Excelente acoplamiento del nudo = Acoplamiento plástico del nudo y excelente seguridad

Empaque hermético = Garantía de estabilidad y esterilidad del producto

ACERCA DE

Recomendado para cualquier procedimiento quirúrgico donde se requiera un monofilamento, sintético absorbible.

Anudado: Cuando se utilizan calibres (2, 1, 0, 2-0) es preferible realizar un doble nudo quirúrgico y después un nudo sencillo. Esto le permitirá al cirujano ajustar la tensión de anudado. Posterior a esto se realizará un nudo cuadrado de acuerdo a las circunstancias y la experiencia del cirujano.

Cuando se utilicen calibres (3-0 al 7-0) se anudará primero con un nudo doble después dos o tres nudos sencillos, dejando las terminaciones del nudo de 4 a 5mm de largo; dependiendo de las circunstancias y de la experiencia del cirujano.

Atramat® PDX

Polydioxanone Polidioxanona



Premium Regular Taper Point
Ahusada Regular Premium

3/8 Circle
Círculo

Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 4-0 EP 1.5
SRE19 19 mm		45 cm	SRE1974-45

Premium Regular Taper Point
Ahusada Regular Premium

1/2 Circle
Círculo

Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 5-0 EP 1	USP 4-0 EP 1.5	USP 3-0 EP 2	USP 2-0 EP 3	USP EP 3.5
SRI7 17 mm		70 cm	SRI775	SRI774	SRI773		
SR20 20 mm		70 cm		SR2074	SR2073		
SR26 26 mm		70 cm		SR2674	SR2673	SR2672	SR2671
SR30 30 mm		70 cm		SR3074	SR3073	SR3072	

Premium Heavy Taper Point
Ahusada Gruesa Premium

1/2 Circle
Círculo

Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 3-0 EP 2	USP 2-0 EP 3	USP 0 EP 3.5	USP 1 EP 4
SG36 36 mm		70 cm 90 cm	SG3673	SG3672	SG3671	SG3678 SG3678-90
SG40 40 mm		70 cm 90 cm			SG4071	SG4078-90
SG48 48 mm		90 cm			SG4871-90	SG4878-90

**Extra Heavy Taper Point**
Ahusada Extra Gruesa**1/2 Circle**
Círculo**Thread Gauge**
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 0 EP 3.5	USP 1 EP 4
X40 40 mm		150 cm Loop	X4071-150LOOP	X4078-150LOOP
X48 48 mm		150 cm Loop	x4871-150LOOP	X4878-150LOOP
X65 65 mm		150 cm Loop		X6578-150LOOP

Premium Reverse Cutting
Reverso Cortante Premium**1/2 Circle**
Círculo**Thread Gauge**
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 3-0 EP 2	USP 2-0 EP 3
P26 26 mm		70 cm	P2673	P2672

Premium Reverse Cutting
Reverso Cortante Premium**3/8 Circle**
Círculo**Thread Gauge**
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 6-0 EP 0.7	USP 5-0 EP 1	USP 4-0 EP 1.5	USP 3-0 EP 2	USP 2-0 EP 3
PE13 13 mm		45 cm	PE1376-45	PE1375-45			
PE19 19 mm		45 cm			PE1974-45	PE1973-45	
PE24 24 mm		45 cm					PE2473-45

Atramat® PDX

Polydioxanone Polidioxanona



Premium Taper Point
Ahusada Premium

1/2 Circle
Círculo

Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 5-0 EP I	USP 4-0 EP 1.5
SI6 16 mm		75 cm	SI675/2	SI674/2
		90 cm		SI674/2-90

Premium Taper Point
Ahusada Premium

3/8 Circle
Círculo

Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 7-0 EP 0.5	USP 6-0 EP 0.7	USP 5-0 EP I
SEI0 10 mm		75 cm	SEI077/2	SEI076/2	
SEI3 13 mm		75 cm		SEI376/2	SEI375/2



Retains 70% tensile strength at 4th week and 50% Tensile strength at 6th week
El material mantiene su resistencia al 70% para el final de la cuarta semana y 50% a la sexta semana.





Atramat® PDX

Polydioxanone Polidioxanona

AtraGlide Cutting
Cortante AtraGlide

3/8 Circle
Círculo



Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 6-0 EP 0.7	USP 5-0 EP 1	USP 4-0 EP 1.5	USP 3-0 EP 2	USP 2-0 EP 3
HPE11 11 mm		45cm Undyed/Incoloro	HPE1176-45B	HPE1175-45B			
HPE13 13 mm		45cm Undyed/Incoloro		HPE1375-45B	HPE1374-45B		
HPE16 16 mm		45cm Undyed/Incoloro		HPE1675-45B	HPE1674-45B		
HPE19 19 mm		45cm Undyed/Incoloro			HPE1974-45B	HPE1973-45B	
HPE24 24 mm		45cm Undyed/Incoloro			HPE2474-45B	HPE2473-45B	HPE2472-45B

Supra-Sharp Reverse Cutting
Reverso Cortante Supra-Sharp

3/8 Circle
Círculo



Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 6-0 EP 0.7	USP 5-0 EP 1	USP 4-0 EP 1.5	USP 3-0 EP 2	USP 2-0 EP 3
P-PE11 11 mm		45cm Undyed/Incoloro	P-PE1176-45B	P-PE1175-45B			
P-PE13 13 mm		45cm Undyed/Incoloro		P-PE1375-45B	P-PE1374-45B		
P-PE16 16 mm		45cm Undyed/Incoloro		P-PE1675-45B	P-PE1674-45B		
P-PE19 19 mm		45cm Undyed/Incoloro			P-PE1974-45B	P-PE1973-45B	
P-PE24 24 mm		45cm Undyed/Incoloro			P-PE2474-45B	P-PE2473-45B	P-PE2472-45B

Supra-Sharp Premium Conventional Cutting
Cortante Convencional Premium Supra-Sharp

3/8 Circle
Círculo



Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 6-0 EP 0.7	USP 5-0 EP 1	USP 4-0 EP 1.5
P-QE13 13 mm		45cm Undyed/Incoloro	P-QE1376-45B	P-QE1375-45B	
P-QE16 16 mm		45cm Undyed/Incoloro		P-QE1675-45B	P-QE1674-45B
P-QE19 19 mm		45cm Undyed/Incoloro			P-QE1974-45B