

Synthetic, absorbable, multifilament braided suture, in an undyed presentation.

Made of polyglycolic acid with polycaprolactone and calcium stearate coating.

The tissue reactivity in microscopic form is minimal.

Absorption occurs through progressive hydrolytic action, completed by 42 days.

The material retains approximately 50% of its tensile strength by the end of the first week.

Color code: Pink.

Frequently used in tissue that requires a short healing period.

CHARACTERISTICS + BENEFITS

High tensile strength = Excellent tissue support.

Braided structure = Excellent handling.

Absorption through hydrolysis = Predictable absorption rate and minimal tissue reaction.

Cylindrical coated multifilament thread = Smooth passage through the tissue.

Excellent knot coupling = Providing excellent security.

Gauge within U.S.P./E.P. guidelines = Less suture material implanted in the tissue.

Hermetically sealed packaging = Ensured stability and sterility of the product.

ABOUT

When implanted in the tissue, the ATRAMAT® Polyglycolic Acid Quick Absorption has minimal tissue reaction on a microscopic basis. This is comparable to other absorbable synthetic sutures of Polyglycolic Acid. However, ATRAMAT® Quick Absorption Polyglycolic Acid, offers a predictable absorption rate and high tensile strength over and above the USP standard, thus providing vital artificial support to the tissue during the critical healing period. The absorption occurs through progressive hydrolytic action completed in approximately 42 days. The material retains approximately 50% of its initial tensile strength at the end of the first week.

The ATRAMAT® Polyglycolic Acid Quick Absorption is coated with Polycaprolactone and Calcium Stearate in the following approximate percentages:

Polyglycolic Acid 99%

Coating1%

Absorbable Sutures

Atramat®PGA
Rapid



Suturas Absorbibles

Atramat® PGA
Rapid

Sutura sintética, absorbible, multifilamento trenzado en color beige.

Compuesto de ácido poliglicólico con un recubrimiento de policaprolactona y estearato de calcio.

La reactividad tisular al microscopio es mínima.

La absorción ocurre a través de una acción hidrolítica progresiva que se completa en 42 días.

El material mantiene su resistencia tensil al 50% para el final de la primera semana.

Código de Color: Rosa.

Frecuentemente utilizado en tejidos con tiempo de cicatrización corto.

CARACTERÍSTICAS + BENEFICIOS

Alta Resistencia tensil = Excelente soporte al tejido

Sutura trenzada = Excelente manipulabilidad

Absorción por hidrólisis = Tasa de absorción predecible y mínima reactividad tisular

Recubrimiento alrededor de la hebra = Paso suave por los tejidos

Excelente acoplamiento del nudo = Acoplamiento plástico del nudo y excelente seguridad

Calibre dentro de los parámetros de la USP = Menor cantidad de material de sutura implantado en el tejido.

Empaque hermético = Garantía de estabilidad y esterilidad del producto.

ACERCA DE

Cuando se implanta en el tejido la sutura de ácido poliglicólico Rapid Atramat® tiene mínima reactividad tisular al microscopio esta en comparación con otros sintéticos absorbibles de ácido poliglicólico. Sin embargo PGA Rapid Atramat® ofrece una tasa de absorción predecible y resistencia tensil de acuerdo a los estándares de la USP, lo que provee un soporte artificial durante el tiempo crítico de cicatrización. La absorción ocurre a través de una acción hidrolítica progresiva, la cual se completa a los 42 días.

El ácido poliglicólico Rapid Atramat® está recubierto con policaprolactona y estearato de calcio en los siguientes porcentajes:

ácido poliglicólico.....99%

Recubrimiento.....1%

Atramat® PGA Rapid



Regular Taper Point Ahusada Regular

1/2 Circle
Círculo

Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 4-0 EP 1.5	USP 3-0 EP 2	USP 2-0 EP 3	USP 1 EP 4
R20 20 mm		75 cm Undyed/Incoloro	R2084-75B	R2083-75B		
R26 26 mm		75 cm Undyed/Incoloro		R2683-75B	R2682-75B	
R30 30 mm		75 cm Undyed/Incoloro			R3082-75B	R3088-75B

Heavy Taper Point Ahusada Gruesa

1/2 Circle
Círculo

Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 3-0 EP 2	USP 2-0 EP 3	USP 0 EP 3.5	USP 1 EP 4
G26 26 mm		70 cm Undyed/Incoloro	G2683-B			
		75 cm Undyed/Incoloro		G3782-75B	G3781-75B	G3788-75B
G37 37 mm		90 cm Undyed/Incoloro		G3782-90B	G3781-90B	G3788-90B
		75 cm Undyed/Incoloro			G4081-75B	G4088-75B
G40 40 mm		90 cm Undyed/Incoloro			G4081-90B	G4088-90B
G48 48 mm		75 cm Undyed/Incoloro				G4888-75B





Premium Regular Taper Point
Ahusada Regular Premium

1/2 Circle
Círculo

Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 5-0 EP 1	USP 4-0 EP 1.5	USP 3-0 EP 2	USP 2-0 EP 3
SR17 17 mm		75 cm Undyed/Incoloro	SR1785-75B	SR1784-75B	SR1783-75B	
SR20 20 mm		75 cm Undyed/Incoloro			SR2083-75B	
SR26 26 mm		75 cm Undyed/Incoloro		SR2684-75B	SR2683-75B	SR2682-75B
SR30 30 mm		75 cm Undyed/Incoloro				SR3082-75B

Premium Heavy Taper Point
Ahusada Gruesa Premium

1/2 Circle
Círculo

Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 2-0 EP 3	USP 0 EP 3.5	USP 1 EP 4
SG36 36 mm		75 cm Undyed/Incoloro	SG3682-75B	SG3681-75B	SG3688-75B
		90 cm Undyed/Incoloro	SG3682-90B	SG3681-90B	
SG40 40 mm		75 cm Undyed/Incoloro		SG4081-75B	SG4088-75B
		90 cm Undyed/Incoloro	SG4082-90B	SG4081-90B	SG4088-90B
SG48 48 mm		90 cm Undyed/Incoloro		SG4881-90B	SG4888-90B





Atramat® PGA Rapid



Reverse Cutting Reverso Cortante

3/8 Circle
Círculo 


Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 4-0 EP 1.5	USP 3-0 EP 2
CE19 19 mm		45 cm Undyed/Incoloro	CEI984-45B	CEI983-45B
		75 cm Undyed/Incoloro	CEI984-75B	CEI983-75B
CE24 24 mm		75 cm Undyed/Incoloro		CE2483-75B

Straight Cutting Recta Cortante






Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 3-0 EP 2
U60 60 mm		75 cm Undyed/Incoloro	U6083-B

Premium Reverse Cutting Reverso Cortante Premium

3/8 Circle
Círculo 


Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 5-0 EP 1	USP 4-0 EP 1.5	USP 3-0 EP 2	USP 2-0 EP 3
PE16 16 mm		75 cm Undyed/Incoloro		PE1684-75B	PE1683-75B	
		45 cm Undyed/Incoloro		PE1984-45B	PE1983-45B	
PE19 19 mm		75 cm Undyed/Incoloro	PE1985-75B	PE1984-75B	PE1983-75B	
PE24 24 mm		75 cm Undyed/Incoloro		PE2484-75B	PE2483-75B	PE2482-75B

Premium Straight Cutting Recta Cortante Premium



Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 2-0 EP 3
PU60 60 mm		75 cm Undyed/Incoloro	PU6082-B





Absorbable Sutures | Suturas Absorbibles


Atramat® PGA Rapid

54

Without Needle
Sin aguja

Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 3-0 EP 2	USP 2-0 EP 3	USP 0 EP 3.5	USP 1 EP 4
SS	Without Needle Sin Aguja	150 cm Undyed/Incoloro	SS0083-150B	SS0082-150B		SS0088-150B
SS	Without Needle Sin Aguja	250 cm Undyed/Incoloro			SS0081-250B	



Retains 50% tensile strength at 1st week

El material mantiene su resistencia tensil el 50% para el final de la primera semana.









Atramat® PGA Rapid

Supra-Sharp Reverse Cutting
Reverso Cortante Supra-Sharp

3/8 Circle
Círculo 

Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 6-0 EP 0.7	USP 5-0 EP 1	USP 4-0 EP 1.5	USP 3-0 EP 2	USP 2-0 EP 3
P-PE11 11 mm		45cm Undyed/Incoloro	P-PE1186-45B	P-PE1185-45B			
P-PE13 13 mm		45cm Undyed/Incoloro		P-PE1385-45B	P-PE1384-45B		
P-PE19 19 mm		45cm Undyed/Incoloro			P-PE1984-45B	P-PE1983-45B	
		75cm Undyed/Incoloro			P-PE1984-75B	P-PE1983-75B	
P-PE24 24 mm		45cm Undyed/Incoloro				P-PE2483-45B	P-PE2482-45B
		75cm Undyed/Incoloro				P-PE2483-75B	P-PE2482-75B








Atramat® PGA

Supra-Sharp Reverse Cutting
Reverso Cortante Supra-Sharp

3/8 Circle
Círculo 

Thread Gauge
Calibre de la Hebra

Type Tipo	Needle Aguja	Length Longitud	USP 6-0 EP 0.7	USP 5-0 EP 1	USP 4-0 EP 1.5	USP 3-0 EP 2	USP 2-0 EP 3
P-PE11 11 mm		45cm Undyed/Incoloro	P-PE1196-45B	P-PE1195-45B			
P-PE13 13 mm		45cm Undyed/Incoloro	P-PE1396-45B	P-PE1395-45B	P-PE1394-45B		
P-PE16 16 mm		45cm Undyed/Incoloro		P-PE1695-45B			
P-PE19 19 mm		45cm Black/ Negro			P-PE1994-45B	P-PE1993-45B	
P-PE24 24 mm		45cm Undyed/Incoloro				P-PE2493-45B	P-PE2492-45B